

YORK/LUXAIRE/FRASER JOHNSTON

CROSS REFERENCE PACKAGE AIR CONDITIONER

D1EB 018-060 (10 SEER)
D1EH 018-060 (12 SEER)
D1EM 048-060 (13 SEER)

Warren Model No.	Luxaire/Fraser Johnston Model No.	Johnston KW	Voltage/Phase	Recommended To Fit:		
WNH0502	2NH04500506	5.0	240/1	D1EB018-060	D1EH018-060	D1EM048-060
WNH0752	2NH04500706	7.5	240/1	D1EB018-060	D1EH018-060;	D1EM048-060
WNH1002	2NH04501006	10.0	240/1	D1EB024-060;	D1EH024-060;	D1EM048-060
WNH1502	2NH04501506	15.0	240/1	D1EB030-060;	D1EH030-060;	D1EM048-060
WNH2002	2NH04502006	20.0	240/1	D1EB048-060;	N/A	D1EM048-060
WNH2502	2NH04502506	25.0	240/1	D1EB048-060;	N/A	D1EM048-060
WNH0504	N/A	5.0	240/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH0754	N/A	7.5	240/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH1004	2NH04501025	10.0	240/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH1504	2NH04501525	15.0	240/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH2004	2NH04502025	20.0	240/3	D1EB048-060;	N/A	D1EM048-060
WNH2504	2NH04502525	25.0	240/3	D1EB048-060;	N/A	D1EM048-060
WNH0505	N/A	5.0	480/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH0755	N/A	7.5	480/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH1005	2NH04501046	10.0	480/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH1505	2NH04501546	15.0	480/3	D1EB036-060;	D1EH030-060;	D1EM048-060
WNH2005	2NH04502046	20.0	480/3	D1EB048-060;	N/A	D1EM048-060
WNH2505	2NH04502546	25.0	480/3	D1EB048-060;	N/A	D1EM048-060
WNH0509	N/A	5.0	600/3	D1EB036-060;	D1EH036-060	N/A
WNH0759	N/A	7.5	600/3	D1EB036-060;	D1EH036-060	N/A
WNH1009	2NH04501058	10.0	600/3	D1EB036-060;	D1EH036-060	N/A
WNH1509	2NH04501558	15.0	600/3	D1EB036-060;	D1EH036-060	N/A
WNH2009	2NH04502058	20.0	600/3	D1EB048-060	D1EH048-060	N/A
WNH2509	2NH04502558	25.0	600/3	D1EB048-060	D1EH048-060	N/A

WARREN TECHNOLOGY

2050 W 73 ST • PO BOX 5347 • HIALEAH, FL 33016-9912 • TEL 305-556-6933 • FAX 305- 557-6157
 Website: www.warrenvac.com

LUXAIRE/FRASER JOHNSTON

CROSS REFERENCE PACKAGE HEAT PUMP

B1HA 018-060 (10 SEER)
B1HH 018-060 (12 SEER)

Warren Model No.	Luxaire/Fraser Johnston Model No.	KW	Voltage/Phase	Recommended to Fit
WNH0502	2NH04500506	5.0	240/1	B1HA018-060; B1HH018-060
WNH0752	2NH04500706	7.5	240/1	B1HA018-060; B1HH018-060
WNH1002	2NH04501006	10.0	240/1	B1HA024-060; B1HH024-060
WNH1502	2NH04501506	15.0	240/1	B1HA030-060; B1HH030-060
WNH1502D	2ND04501506	15.0	240/1	B1HA030-042; B1HH030-042
WNH2002	2NH04502006	20.0	240/1	B1HA048-060; B1HH048-060
WNH2502	2NH04502506	25.0	240/1	B1HA048-060; B1HH048-060
WNH0504	N/A	5.0	240/3	B1HA036-060; B1HH030-060
WNH0754	N/A	7.5	240/3	B1HA036-060; B1HH030-060
WNH1004	2NH04501025	10.0	240/3	B1HA036-060; B1HH030-060
WNH1504	2NH04501525	15.0	240/3	B1HA036-060; B1HH030-060
WNH2004	2NH04502025	20.0	240/3	B1HA048-060; B1HH048-060
WNH2504	2NH04502525	25.0	240/3	B1HA048-060; B1HH048-060
WNH0505	N/A	5.0	480/3	B1HA036-060; B1HH030-060
WNH0755	N/A	7.5	480/3	B1HA036-060; B1HH030-060
WNH1005	2NH04501046	10.0	480/3	B1HA036-060; B1HH030-060
WNH1505	2NH04501546	15.0	480/3	B1HA036-060; B1HH030-060
WNH2005	2NH04502046	20.0	480/3	B1HA048-060; B1HH048-060
WNH2505	2NH04502546	25.0	480/3	B1HA048-060; B1HH048-060
WNH0509	N/A	5.0	600/3	B1HA036-060; B1HH036-060
WNH0759	N/A	7.5	600/3	B1HA036-060; B1HH036-060
WNH1009	2NH04501058	10.0	600/3	B1HA036-060; B1HH036-060
WNH1509	2NH04501558	15.0	600/3	B1HA036-060; B1HH036-060
WNH2009	2NH04502058	20.0	600/3	B1HA048-060; B1HH048-060
WNH2509	2NH04502558	25.0	600/3	B1HA048-060; B1HH048-060

WARREN TECHNOLOGY

2050 W 73 ST • PO BOX 5347 • HIALEAH, FL 33016-9912 • TEL 305-556-6933 • FAX 305-557-6157

**YORK/LUXAIRE/FRASER JOHNSTON
CROSS REFERENCE
PACKAGE AIR CONDITIONER**

D*EZ 024-060 (13 SEER)

D*EQ 024-060 (14 SEER)

D*EX 024-060 (15 SEER)

D*EY 060 (14 SEER)

D*PB 036-060 (10 SEER)

WARREN Model No.	Luxaire/Fraser J. Model No.	KW	Voltage/ Phase	Recommended to Fit				
				D*EZ	D*EQ	D*EX	D*EY	D*PB
WNH0502	2NH04500506	5.0	240/1	024-042	024-042	024-042	60	N/A
WNH0752	2NH04500706	7.5	240/1	024-042	024-042	024-042	60	N/A
WNH1002	2NH04501006	10.0	240/1	024-060	024-060	024-048	60	N/A
WNH1502	2NH04501506	15.0	240/1	030-060	030-060	024-048	60	N/A
WNH2002	2NH04502006	20.0	240/1	048-060	048-060	48	60	N/A
WNH2502	2NH04502506	25.0	240/1	048-060	048-060	48	60	N/A
WNH0504	N/A	5.0	240/3	036-060	036-060	036-048	60	036-060
WNH0754	N/A	7.5	240/3	036-060	036-060	036-048	60	036-060
WNH1004	2NH04501025	10.0	240/3	036-060	036-060	036-048	60	036-060
WNH1504	2NH04501525	15.0	240/3	036-060	036-060	036-048	60	036-060
WNH2004	2NH04502025	20.0	240/3	048-060	048-060	48	60	048-060
WNH2504	2NH04502525	25.0	240/3	048-060	048-060	48	60	048-060
WNH0505	N/A	5.0	480/3	036-060	036-060	036-060	60	036-060
WNH0755	N/A	7.5	480/3	036-060	036-060	036-060	60	036-060
WNH1005	2NH04501046	10.0	480/3	036-060	036-060	036-048	60	036-060
WNH1505	2NH04501546	15.0	480/3	036-060	036-060	036-048	60	036-060
WNH2005	2NH04502046	20.0	480/3	048-060	048-060	48	60	048-060
WNH2505	2NH04502546	25.0	480/3	048-060	048-060	48	60	048-060
WNH0509	N/A	5.0	600/3	036-060	036-060	N/A	N/A	036-060
WNH0759	N/A	7.5	600/3	036-060	036-060	N/A	N/A	036-060
WNH1009	2NH04501058	10.0	600/3	036-060	036-060	N/A	N/A	036-060
WNH1509	2NH04501558	15.0	600/3	036-060	036-060	N/A	N/A	036-060
WNH2009	2NH04502058	20.	600/3	048-060	048-060	N/A	N/A	048-060
WNH25092	2NH04502558	25.0	600/3	048-060	048-060	N/A	N/A	048-060

* DENOTES 1, 2, A, B

WARREN TECHNOLOGY

2050 W 73 ST. * PO BOX 5347 * HIALEAH, FL 33016-9912 * TEL 305-556-6933 * FAX 305-557-6157

Website: www.warrenhvac.com

**YORK/LUXAIRE/FRASER JOHNSTON
CROSS REFERENCE
PACKAGE HEAT PUMP**

**B*UH 018-060 (12 SEER)
B*HQ 024-060 (14 SEER)
B*HX 024-060 (15 SEER)
B*UQ 024-060 (14 SEER)
B*UX 024-060 (15 SEER)**

WARREN Model No.	Luxaire/Fraser J. Model No.	KW	Voltage/ Phase	Recommended to Fit				
				B*UH	B*HQ	B*HX	B*UQ	B*UX
WNH0502	2NH04500506	5.0	240/1	018-036	024-036	024-036	024-036	024-036
WNH0752	2NH04500706	7.5	240/1	018-036	024-036	024-036	024-036	024-036
WNH1002	2NH04501006	10.0	240/1	024-060	024-060	024-060	024-060	024-060
WNH1502	2NH04501506	15.0	240/1	030-060	030-060	036-060	030-060	030-060
WNH2002	2NH04502006	20.0	240/1	048-060	048-060	048-060	048-060	048-060
WNH2502	2NH04502506	25.0	240/1	048-060	048-060	048-060	048-060	048-060
WNH0504	N/A	5.0	240/3	030-060	030-060	036-060	030-060	036-060
WNH0754	N/A	7.5	240/3	030-060	030-060	036-060	030-060	036-060
WNH1004	2NH04501025	10.0	240/3	030-060	030-060	036-060	030-060	036-060
WNH1504	2NH04501525	15.0	240/3	030-060	030-060	036-060	030-060	036-060
WNH2004	2NH04502025	20.0	240/3	048-060	048-060	048-060	048-060	048-060
WNH2504	2NH04502525	25.0	240/3	048-060	048-060	048-060	048-060	048-060
WNH0505	N/A	5.0	480/3	030-060	030-060	036-060	030-060	036-060
WNH0755	N/A	7.5	480/3	030-060	030-060	036-060	030-060	036-060
WNH1005	2NH04501046	10.0	480/3	030-060	030-060	036-060	030-060	036-060
WNH1505	2NH04501546	15.0	480/3	030-060	030-060	036-060	030-060	036-060
WNH2005	2NH04502046	20.0	480/3	048-060	048-060	048-060	048-060	048-060
WNH2505	2NH04502546	25.0	480/3	048-060	048-060	048-060	048-060	048-060
WNH0509	N/A	5.0	600/3	030-060	N/A	N/A	N/A	N/A
WNH0759	N/A	7.5	600/3	030-060	N/A	N/A	N/A	N/A
WNH1009	2NH04501058	10.0	600/3	030-060	N/A	N/A	N/A	N/A
WNH1509	2NH04501558	15.0	600/3	030-060	N/A	N/A	N/A	N/A
WNH2009	2NH04502058	20.	600/3	048-060	N/A	N/A	N/A	N/A
WNH25092	2NH04502558	25.0	600/3	048-060	N/A	N/A	N/A	N/A

* DENOTES 1, 2, A, B

WARREN TECHNOLOGY
2050 W 73 ST. * PO BOX 5347 * HIALEAH, FL 33016-9912 * TEL 305-556-6933 * FAX 305-557-6157
Website: www.warrenhvac.com

COLEMAN CROSS REFERENCE PACKAGE AIR CONDITIONER

**DAPB 018-060 (10 SEER)
DAPH 018-060 (12 SEER)
DAPM 048-060 (13 SEER)**

Warren Model No.	York Model No.	KW	Voltage/ Phase	Recommended To Fit.		
WNH0502	2NH04500506	5.0	240/1	DAPB018-060;	DAPH 018-060;	DAPM048-060
WNH0752	2NH04500706	7.5	240/1	DAPB018-060;	DAPH 018-060;	DAPM048-060
WNH1002	2NH04501006	10.0	240/1	DAPB024-060;	DAPH 024-060;	DAPM048-060
WNH1502	2NH04501506	15.0	240/1	DAPB030-060;	DAPH 030-060;	DAPM048-060
WNH2002	2NH04502006	20.0	240/1	DAPB048-060;	N/A	DAPM048-060
WNH2502	2NH04502506	25.0	240/1	DAPB048-060;	N/A	DAPM048-060
WNH0504	N/A	5.0	240/3	DAPB036-060;	DAPH 030-060;	DAPM048-060
WNH0754	N/A	7.5	240/3	DAPB036-060;	DAPH 030-060;	DAPM048-060
WNH1004	2NH04501025	10.0	240/3	DAPB036-060;	DAPH 030-060;	DAPM048-060
WNH1504	2NH04501525	15.0	240/3	DAPB036-060;	DAPH 030-060;	DAPM048-060
WNH2004	2NH04502025	20.0	240/3	DAPB048-060;	N/A	DAPM048-060
WNH2504	2NH04502525	25.0	240/3	DAPB048-060;	N/A	DAPM048-060
WNH0505	N/A	5.0	480/3	DAPB036-060;	DAPH030-060;	DAPM048-060
WNH0755	N/A	7.5	480/3	DAPB036-060;	DAPH030-060;	DAPM048-060
WNH1005	2NH04501046	10.0	480/3	DAPB036-060;	DAPH030-060;	DAPM048-060
WNH1505	2NH04501546	15.0	480/3	DAPB036-060;	DAPH030-060;	DAPM048-060
WNH2005	2NH04502046	20.0	480/3	DAPB048-060;	N/A	DAPM048-060
WNH2505	2NH04502546	25.0	480/3	DAPB048-060;	N/A	DAPM048-060
WNH0509	N/A	5.0	600/3	DAPB036-060;	DAPH036-060	N/A
WNH0759	N/A	7.5	600/3	DAPB036-060;	DAPH036-060	N/A
WNH1009	2NH04501058	10.0	600/3	DAPB036-060;	DAPH036-060	N/A
WNH1509	2NH04501558	15.0	600/3	DAPB036-060;	DAPH036-060	N/A
WNH2009	2NH04502058	20.0	600/3	DAPB048-060	DAPH048-060	N/A
WNH2509	2NH04502558	25.0	600/3	DAPB048-060	DAPH048-060	N/A

WARREN TECHNOLOGY

2050 W 73 ST • PO BOX 5347 • HIALEAH, FL 33016-9912 • TEL 305-556-6933 • FAX 305- 557-6157
Website: www.warrenvac.com

COLEMAN CROSS REFERENCE PACKAGE HEAT PUMP

**BAUA 018-060 (10 SEER)
BAUH 018-060 (12 SEER)**

Warren Model No.	York Model No.	KW	Voltage/ Phase	Recommended To Fit
WNH0502	2NH04500506	5.0	240/1	BAUA018-060; BAUH018-060
WNH0752	2NH04500706	7.5	240/1	BAUA018-060; BAUH018-060
WNH1002	2NH04501006	10.0	240/1	BAUA024-060; BAUH024-060
WNH1502	2NH04501506	15.0	240/1	BAUA030-060; BAUH030-060
WNH1502D	2ND04501506	15.0	240/1	BAUA030-042; BAUH030-042
WNH2002	2NH04502006	20.0	240/1	BAUA048-060; BAUH048-060
WNH2502	2NH04502506	25.0	240/1	BAUA048-060; BAUH048-060
WNH0504	N/A	5.0	240/3	BAUA036-060; BAUH030-060
WNH0754	N/A	7.5	240/3	BAUA036-060; BAUH030-060
WNH1004	2NH04501025	10.0	240/3	BAUA036-060; BAUH030-060
WNH1504	2NH04501525	15.0	240/3	BAUA036-060; BAUH030-060
WNH2004	2NH04502025	20.0	240/3	BAUA048-060; BAUH048-060
WNH2504	2NH04502525	25.0	240/3	BAUA048-060; BAUH048-060
WNH0505	N/A	5.0	480/3	BAUA036-060; BAUH030-060
WNH0755	N/A	7.5	480/3	BAUA036-060; BAUH030-060
WNH1005	2NH04501046	10.0	480/3	BAUA036-060; BAUH030-060
WNH1505	2NH04501546	15.0	480/3	BAUA036-060; BAUH030-060
WNH2005	2NH04502046	20.0	480/3	BAUA048-060; BAUH048-060
WNH2505	2NH04502546	25.0	480/3	BAUA048-060; BAUH048-060
WNH0509	N/A	5.0	600/3	BAUA036-060; BAUH036-060
WNH0759	N/A	7.5	600/3	BAUA036-060; BAUH036-060
WNH1009	2NH04501058	10.0	600/3	BAUA036-060; BAUH036-060
WNH1509	2NH04501558	15.0	600/3	BAUA036-060; BAUH036-060
WNH2009	2NH04502058	20.0	600/3	BAUA048-060; BAUH048-060
WNH2509	2NH04502558	25.0	600/3	BAUA048-060; BAUH048-060

WARREN TECHNOLOGY

2050 W 73 ST • PO BOX 5347 • HIALEAH, FL 33016-9912 • TEL 305-556-6933 • FAX 305-557-6157
Website: www.warrenhvac.com